

Technical drawing of a mechanical assembly, showing three views: front view (top), side view (middle), and top view (bottom). The drawing includes various dimension lines and labels (A through M) indicating specific measurements and features.


Front View (Top): Shows the main body of the assembly. Key dimensions include a total width of 10.30 (A), a central width of 8.64 (B), and a smaller central width of 7.50 (C). The height of the main body is 11.60 (E). The distance from the bottom of the main body to the center of the mounting holes is 4.00 (F). The distance between the mounting holes is 2.40 (D). The distance from the center of the mounting holes to the center of the main body is 1.00. The diameter of the mounting holes is $\phi 1.1$.

Side View (Middle): Shows the side profile of the assembly. Key dimensions include a total width of 10.30 (A), a central width of 8.64 (B), and a smaller central width of 7.50 (C). The height of the main body is 11.60 (E). The distance from the bottom of the main body to the center of the mounting holes is 4.00 (F). The distance between the mounting holes is 2.40 (D). The distance from the center of the mounting holes to the center of the main body is 1.00. The diameter of the mounting holes is $\phi 1.1$.

Top View (Bottom): Shows the top of the assembly. Key dimensions include a total width of 13.60 (S), a central width of 4.72 (H), and a smaller central width of 1.22. The distance from the bottom of the main body to the center of the mounting holes is 4.00 (F). The distance between the mounting holes is 2.40 (D). The distance from the center of the mounting holes to the center of the main body is 1.00. The diameter of the mounting holes is $\phi 1.1$.

Labels and Dimensions:

- A: 10.30
- B: 8.64
- C: 7.50
- D: 2.40
- E: 11.60
- F: 4.00
- G: $\phi 0.60$
- H: 4.72
- I: 1.22
- J: 7.20
- K: 15.35
- L: 17.70
- M: 3-3.50
- N: 1.30
- O: 1.75
- P: 9.80
- Q: 9.80
- R: 1.30
- S: 13.60
- T: 1.00
- U: $\phi 1.1$
- V: 1.60
- W: 2.40
- X: 4.00
- Y: 1.60
- Z: 2.40
- AA: 4.00
- AB: 1.60
- AC: 2.40
- AD: 4.00
- AE: 1.60
- AF: 2.40
- AG: 4.00
- AH: 1.60
- AI: 2.40
- AJ: 4.00
- AK: 1.60
- AL: 2.40
- AM: 4.00
- AN: 1.60
- AO: 2.40
- AP: 4.00
- AQ: 1.60
- AR: 2.40
- AS: 4.00
- AT: 1.60
- AU: 2.40
- AV: 4.00
- AW: 1.60
- AX: 2.40
- AY: 4.00
- AZ: 1.60
- BA: 2.40
- BB: 4.00
- BC: 1.60
- BD: 2.40
- BE: 4.00
- BF: 1.60
- BG: 2.40
- BH: 4.00
- BI: 1.60
- BJ: 2.40
- BK: 4.00
- BL: 1.60
- BM: 2.40
- BN: 4.00
- BO: 1.60
- BP: 2.40
- BQ: 4.00
- BR: 1.60
- BS: 2.40
- BT: 4.00
- BU: 1.60
- BV: 2.40
- BW: 4.00
- BX: 1.60
- BY: 2.40
- BZ: 4.00
- CA: 1.60
- CB: 2.40
- CC: 4.00
- CD: 1.60
- CE: 2.40
- CF: 4.00
- CG: 1.60
- CH: 2.40
- CI: 4.00
- CJ: 1.60
- CK: 2.40
- CL: 4.00
- CM: 1.60
- CN: 2.40
- CO: 4.00
- CP: 1.60
- CQ: 2.40
- CR: 4.00
- CS: 1.60
- CT: 2.40
- CU: 4.00
- CV: 1.60
- CW: 2.40
- CV: 4.00
- CA: 1.60
- CB: 2.40
- CC: 4.00
- CD: 1.60
- CE: 2.40
- CF: 4.00
- CG: 1.60
- CH: 2.40
- CI: 4.00
- CJ: 1.60
- CK: 2.40
- CL: 4.00
- CM: 1.60
- CN: 2.40
- CO: 4.00
- CP: 1.60
- CQ: 2.40
- CR: 4.00
- CS: 1.60
- CT: 2.40
- CU: 4.00
- CV: 1.60
- CW: 2.40
- CV: 4.00
- CA: 1.60
- CB: 2.40
- CC: 4.00
- CD: 1.60
- CE: 2.40
- CF: 4.00
- CG: 1.60
- CH: 2.40
- CI: 4.00
- CJ: 1.60
- CK: 2.40
- CL: 4.00
- CM: 1.60
- CN: 2.40
- CO: 4.00
- CP: 1.60
- CQ: 2.40
- CR: 4.00
- CS: 1.60
- CT: 2.40
- CU: 4.00
- CV: 1.60
- CW: 2.40
- CV: 4.00
- CA: 1.60
- CB: 2.40
- CC: 4.00
- CD: 1.60
- CE: 2.40
- CF: 4.00
- CG: 1.60
- CH: 2.40
- CI: 4.00
- CJ: 1.60
- CK: 2.40
- CL: 4.00
- CM: 1.60
- CN: 2.40
- CO: 4.00
- CP: 1.60
- CQ: 2.40
- CR: 4.00
- CS: 1.60
- CT: 2.40
- CU: 4.00
- CV: 1.60
- CW: 2.40
- CV: 4.00
- CA: 1.60
- CB: 2.40
- CC: 4.00
- CD: 1.60
- CE: 2.40
- CF: 4.00
- CG: 1.60
- CH: 2.40
- CI: 4.00
- CJ: 1.60
- CK: 2.40
- CL: 4.00
- CM: 1.60
- CN: 2.40
- CO: 4.00
- CP: 1.60
- CQ: 2.40
- CR: 4.00
- CS: 1.60
- CT: 2.40
- CU: 4.00
- CV: 1.60
- CW: 2.40
- CV: 4.00
- CA: 1.60
- CB: 2.40
- CC: 4.00
- CD: 1.60
- CE: 2.40
- CF: 4.00
- CG: 1.60
- CH: 2.40
- CI: 4.00
- CJ: 1.60
- CK: 2.40
- CL: 4.00
- CM: 1.60
- CN: 2.40
- CO: 4.00
- CP: 1.60
- CQ: 2.40
- CR: 4.00
- CS: 1.60
- CT: 2.40
- CU: 4.00
- CV: 1.60
- CW: 2.40
- CV: 4.00
- CA: 1.60
- CB: 2.40
- CC: 4.00
- CD: 1.60
- CE: 2.40
- CF: 4.00
- CG: 1.60
- CH: 2.40
- CI: 4.00
- CJ: 1.60
- CK: 2.40
- CL: 4.00
- CM: 1.60
- CN: 2.40
- CO: 4.00
- CP: 1.60
- CQ: 2.40
- CR: 4.00
- CS: 1.60
- CT: 2.40
- CU: 4.00
- CV: 1.60
- CW: 2.40
- CV: 4.00
- CA: 1.60
- CB: 2.40
- CC: 4.00
- CD: 1.60
- CE: 2.40
- CF: 4.00
- CG: 1.60
- CH: 2.40
- CI: 4.00
- CJ: 1.60
- CK: 2.40
- CL: 4.00
- CM: 1.60
- CN: 2.40
- CO: 4.00
- CP: 1.60
- CQ: 2.40
- CR: 4.00
- CS: 1.60
- CT: 2.40
- CU: 4.00
- CV: 1.60
- CW: 2.40
- CV: 4.00
- CA: 1.60
-



SHENZHEN BOSCOM ELECTRONICS CO.,LTD

深圳市观澜街道石马径社区君新路
石三工业区146号

0755-28032965

0<L≤4	±0.10	
4<L≤16	±0.20	壁厚: ±0.10
16以上	±0.30	PIN径: ±0.05